

## **Assembly Instruction**

Inside Cabinet Dimension

Front Panel Mounting Positions

Front Fixing Brackets Positions


Back Panel Mounting Positions


## Special Features:


- Length:270,300,350,400,450,500,550mm.
- The drawer side-board is 171mm high.
  Drawer width can be designed freely with automatic error adjustment.
- Hidden full pullout silencing sliding skid can bear 40kg and enjoys
- excellent stability and quite and smooth sliding performance. Quick installation and dismantle.
- Newly-designed built-in damper is free from reinstallation and ensures soft and smooth drawer movements.

550mm	500mm	450mm	400mm	350 mm	300mm	Basic length
524mm	474mm	424mm	374mm	324mm	274mm	Internally usable drawer depth
550mm	500mm	450mm	400mm	350mm	300mm	Minimum installation depth of drawer
192mm	192mm	192mm	192mm	192mm	192mm	Minimum installation height










Mounting the drawer



Technology pivot:
Bottom and Back Panel Measurement
16MM Density Panel



Installing the drawer



Function of the damper

2


Back panel height= 151MM

Back panel width=Inside Cabinet Width-87±0.5

Bottom panel width=Inside Cabinet Width-75±0.5
 Rottom panel length=Runner length-10MM

LW:Inside Cabinet Width

Bottom panel length=Runner length-10MM



Tighten the fixing screw after instilled the panel
 Press the upper pin into panel after installed the panel

Take out the plasic cover
Take out the upper pin

Loosen the fastening screwsRotation to dismantle the panel

Front panel removing A.B Side pverlay(user-defined) . В

B Side overlay(user: ak

efined)
























Removing the drawer











Push the metal spring part from the panel & pull out